




PRODUCT TYPE EC*X

Single Compression Barrier Gland for Unarmoured cable featuring Peppers T2000 or T1000 Compound

Ex db : Ex eb : Ex nR : Ex ta : IP66 : IP68 : IP69



PART NUMBERS:

EC	1	X	B
	2		S

PRODUCT DESCRIPTION

"EC*-X" type glands, approved for use with any shape cable, are certified Flameproof Ex db, Increased Safety Ex eb, Restricted Breathing Ex nR and Dust Protected Ex ta. They are suitable for use in Group I Mining, Zone 1 and 2 for Gas Groups IIA, IIB and IIC and additionally for use in Zones 20, 21 and 22 for Dusts Groups IIIA, IIIB and IIIC. Occasionally referred to as "potting glands", they provide a compound barrier Ex db & IP seal on the cable inner cores (or flying leads), eliminating damage to cables that exhibit "cold flow" characteristics. The unique features include, Peppers T1000 or T2000 compound that enables a quick and easy installation. An innovative barrier chamber that allows for a full inspection of the compound fill. The gland maintains IP66, IP68 to 100 metres and IP 69. Is deluge proof without the use of an additional seal or deluge boot. It is supplied with an IP O-ring seal as standard on metric entry threads.

COMPLIANCE STANDARDS:

EN 60079-0, EN 60079-1, EN 60079-7, EN 60079-15, EN 60079-31
IEC 60079-0, IEC 60079-1, IEC 60079-7, IEC 60079-15, IEC 60079-31 & IEC 60529

CERTIFICATION:

ATEX	I M2 II 1D 2G Ex db I Mb / Ex db IIC Gb / Ex eb I Mb / Ex eb IIC Gb / Ex ta IIIC Da II 3G Ex nR IIC Gc
IECEX	Ex db I Mb / Ex db IIC Gb / Ex eb I Mb / Ex eb IIC Gb / Ex nR IIC Gc / Ex ta IIIC Da
CCC - China	Certificate Pending
CCoE - India	Ex db I Mb / Ex db IIC Gb / Ex eb I Mb / Ex eb IIC Gb / Ex nR IIC Gc
ABS	Specified ABS Rule
LLOYD'S	Ex db I Mb / Ex db IIC Gb / Ex eb I Mb / Ex eb IIC Gb / Ex nR IIC Gc / Ex ta IIIC Da

CERTIFICATION NO.:

ATEX	CML 19ATEX1113X & CML 19ATEX4114X
IECEX	IECEX CML 19.0035X
CCC - China	Certificate Pending
CCoE - India	PESO P494321/17 & P494321/20
ABS	20-LD1944057-PDA
LLOYD'S	LR2124442TA

EXAMPLE PART NUMBERING: EC2-XB/NP/20/M20

EC	Eclipse style barrier gland for use with Peppers T1000 or T2000 compound
2	Peppers T1000 (1) - Peppers T2000 (2)
X	Gland featuring single compression compound (Barrier) Inner Seal for use with unarmoured cable
B	Brass (B) / Stainless Steel (S)
C	PVC Shroud (C) - PCP Shroud (P) - LSOH Shroud (3)
K - V - H	Locknut & Nylon (K), Fibre (V) or PTFE (H) IP Washer
T	Including Earth Tag
S	Including Serrated Washer
1	Quantity per kit
NP	Nickel Plated
20	Gland shell size
M20	M20 Entry Thread

OPTIONAL ACCESSORIES:

LOCKNUT	Brass (ACBLN) / Stainless Steel (ACSLN)
EARTH TAG	Brass (ACBET) / Stainless Steel (ACSET)
IP WASHERS	Nylon (ACNSW) / Fibre (ACFSW) / PTFE (ACPSW)
SERRATED WASHERS	Stainless Steel (ACSSW)
SHROUDS	PVC (ACSPVC) / PCP (ACSPCP) / LSOH (ACSSIO)

IP RATING:	IP66 & IP68 (100 metres - 7 days) & IP69
OPERATING TEMP.:	T1000: -60°C to +135°C T2000: -60°C to +120°C
MATERIALS:	Brass or Stainless Steel
PLATING:	Electroless Nickel
COMPOUND:	Peppers T-1000 Compound / Peppers T-2000 Compound

Eclipse featuring the New T2000 Compound

- Hand operated No Mixing VMS Cartridge
- Fast setting compound. Conductor termination can be effected from 60 minutes @ 23°C
- Featuring Peppers unique "no ferrule" technology allowing it to be fully retractable and inspectable
- Robust Compound for extreme conditions
- Deluge proof without the requirements of additional seals or boots
- Built in interface seal with metric threads

CABLE GLAND SELECTION TABLE (ALL DIMENSIONS IN mm)

Gland size	Entry Thread Size		Metric Thread Length [B]	Gland Sealing Range - Cable Sheath & Cores					Nominal Protrusion Length [L]	Dimensions/Weight (Metric)			Shroud Size* (Metric)
	Metric	NPT		Max Number of Cores [C] [T1000]	Max Number of Cores [C] [T2000]	Max Ø Over Cores [C]	Min Inner Sheath [T2000]	Max Outer Sheath [D]		Across Flats [A]	Across Corners	Weight (Kgs)	
16S	M16 x 1.5	3/8"	16	12	12	8.9	4.0	10.0	36	25.4	28.0	0.089	L24
20S	M20 x 1.5	1/2" or 3/4"	16	35	15	10.4	4.0	11.7	36	25.4	28.0	0.104	L24**
20	M20 x 1.5	1/2" or 3/4"	16	40	20	12.5	4.0	14.0	37	30.0	33.0	0.144	L30
25	M25 x 1.5	3/4" or 1"	16	60	30	16.5	8.0	18.5	42	37.6	41.4	0.226	L38
32	M32 x 1.5	1" or 1 1/4"	16	80	50	23.5	14.0	26.3	45	46.0	50.6	0.358	L46
40	M40 x 1.5	1 1/4" or 1 1/2"	16	130	65	28.8	16.0	32.2	45	55.0	60.5	0.515	L55
50S	-	1 1/2"	16	200	100	34.2	20.0	38.2	54	65.0	71.5	0.675	L65
50	M50 x 1.5	2"	16	400	100	39.4	20.0	44.1	54	65.0	71.5	0.675	L65
63S	-	2"	19	400	130	44.8	30.0	50.1	53	80.0	88.0	0.993	L80
63	M63 x 1.5	2 1/2"	19	425	130	50.0	30.0	56.0	53	80.0	88.0	0.993	L80
75S*	-	2 1/2"	19	425	-	55.4	-	62.0	55	90.0	99.0	1.106	L90
75*	M75 x 1.5	3" or 3 1/2"	19	425	-	60.8	-	68.0	55	90.0	99.0	1.106	L90
80*	M80 x 2.0	3" or 3 1/2"	25	425	-	64.4	-	72.0	66	104.7	115.2	2.098	L104
85*	M85 x 2.0	3" or 3 1/2"	25	425	-	69.8	-	78.0	66	104.7	115.2	1.770	L104
90*	M90 x 2.0	3 1/2" or 4"	25	425	-	75.1	-	84.0	63	114.3	125.7	2.192	L114
100*	M100 x 2.0	3 1/2" or 4"	25	425	-	80.5	-	90.0	65	114.3	125.7	1.847	L114

NOTES

- Gland size does not necessarily equate to the entry thread size.
- The IP O-ring seal is only available on metric entry threads. IP washers can be supplied for tapered entry threads
- Dimensions (A) & (B) may differ for glands with non metric entry threads. Please refer to our "Thread Reference Tables" for specific dimensions.
- Assembly instructions must be read prior to installation and adhered to in full.
- Peppers supplies cable glands with parallel entry threads that conform to the flameproof threaded joint requirements of IEC/EN 60079-1 and other equivalent standards. We usually incorporate a thread run out according to general machining techniques and parts will not

- have a full form thread for the entire length. Peppers Cable Glands Limited will not be held responsible for clients' installations where this has not been taken into account.
- When selecting IP Washer & Shroud material for use with glands, please be aware of the accessories temperature range to ensure they are suitable for the intended installation.
- The gland is supplied with the correct amount of compound, gloves and instructions to allow one complete termination.
- * Size 75S and above only available with T1000 Compound.
- ** For gland sizes 20S when used with 3/4" NPT entry thread an L30 shroud would be required.