




PRODUCT TYPE A8

Single Compression Gland Designed for Armoured and unarmoured cables

Ex db : Ex eb : Ex nR : Ex ta : IP66 : IP68 : Class I Div 2 : AEx e : AEx ta



REFERENCE NUMBER: 3.1.0

PART NUMBERS:

A	8	B	F
S			



PRODUCT DESCRIPTION

"A8" type glands are certified Flameproof Ex db, Increased Safety Ex eb, Restricted Breathing Ex nR and Dust Protected Ex ta. They are suitable for use in Zone 1 and 2 for Gas Groups IIA, IIB and IIC and additionally for use in Zones 20, 21 and 22 for Dust Groups IIIA, IIIB and IIIC. Developed for flat cables, they provide controlled Ex d sealing and have been tested to IP66 and IP68 to 50 metres. The A8 version is designed to accommodate unarmoured and armoured cables where sealing and retention is required only on the outer sheath.

COMPLIANCE STANDARDS:

EN 60079-0, EN 60079-1, EN 60079-7, EN 60079-15, EN 60079-31
IEC 60079-0, IEC 60079-1, IEC 60079-7, IEC 60079-31 & IEC 60529 UL514B, UL1203, ANSI/UL 60079-0/7, ISA 60079-31

EXAMPLE PART NUMBERING:
ABBF/NP/20R/M20

A	Gland for Unarmoured Cables
8	Silicone Seal for flat cables
B	Brass (B) / Stainless Steel (S)
F	Multiple Certification
NP	Nickel Plated
20R	Gland shell size
M20	M20 x 1.5mm Male Entry Thread

OPTIONAL ACCESSORIES:

LOCKNUT	Brass (ACBLN) / Stainless Steel (ACSLN)
EARTH TAG	Brass (ACBET) / Stainless Steel (ACSET)
IP WASHERS	Nylon (ACNSW) / Fibre (ACFSW) / PTFE (ACPSW)
SERRATED WASHERS	Stainless Steel (ACSSW)

IP RATING:	IP66 & IP68 (50 metres - 7 Days)
OPERATING TEMP:	Silicone Seals -60°C to +180°C
MATERIALS:	Brass or Stainless Steel
PLATING:	Electroless Nickel

CERTIFICATION:

ATEX	II 1D 2G Ex db IIC Gb / Ex eb IIC Gb / Ex ta IIIC Da II 3G Ex nR IIC Gc
IECEX	Ex db IIC Gb / Ex eb IIC Gb / Ex ta IIIC Da
NEC – USA	Class II Division 1, Groups E, F & G Class III, Enclosure Type 4X Class I Zone 1 AEx e IIC Gb Class II Zone 20 AEx ta IIIC Da
EAC	1Ex d II Gb X / 1Ex e IIC Gb X / 2Ex nR IIC Gc X / Ex ta IIIC Da X
INMETRO – Brazil	Ex db IIC Gb / Ex eb IIC Gb / Ex ta IIIC Da / Ex nR IIC Gc
SAC – China	Ex d IIC Gb / Ex e IIC Gb
UKRAINE	Ex d IIC X / Ex e II X
CCoE – India	Ex d IIC Gb (Zone 1) Ex e IIC Gb (Zone 2) Ex nR IIC Gc (Zone 2)
ABS	Specified ABS Rules
LLOYD'S	Ex d IIC Gb / Ex e IIC Gb / Ex nR IIC Gc / Ex ta IIIC Da
RMRS	Ex d IC / Ex d IIC / Ex e IC / Ex e IIC / Ex ta IIIC / Ex tb IIIC

CERTIFICATION No:

ATEX	SIRA 01ATEX1270X & SIRA 09ATEX1221X
IECEX	IECEX SIR 05.0020X
NEC – USA	CSA 2627370
EAC	TC RU C-GB.BH02.B.00693-18
INMETRO – Brazil	NCC 13.2187 X
SAC – China	NEPSI GYJ16.1398X
UKRAINE	UA.TR.047.C.0408-13 & 2937
CCoE – India	PESO P365300/2 & P365300/6
ABS	14-LD463991-1-PDA
LLOYD'S	10/00056(E1)
RMRS	14.02755.315

CABLE GLAND SELECTION TABLE
(ALL DIMENSIONS IN mm)

Gland Size	Entry Thread Size		ISO Thread Length [B]	Cable Outer Sheath [D]				Nominal Protrusion Length [L]	Dimensions/Weight (Metric)			Shroud Size (Metric)
	Metric	NPT		Width		Thickness			Across Flats [A]	Across Corners	Weight Kgs (Metric)	
				Min	Max	Min	Max					
20S	M20 x 1.5	3/4" or 1/2"	16	6.3	11.7	4.0	7.0	33	30.0	33.0	0.104	N/A
	M25 x 1.5											
20R	M20 x 1.5	3/4" or 1/2"	16	8.1	13.5	5.8	6.2	33	30.0	33.0	0.104	N/A
	M25 x 1.5											
20	M20 x 1.5 M25 x 1.5	3/4" or 1/2"	16	10.3	13.5	5.6	9.0	33	30.0	33.0	0.103	N/A
** 25	M25 x 1.5	3/4" or 1"	16	10.6	16.2	4.0	7.0	31	37.6	41.4	0.162	N/A

NOTES

- ** Size 25mm is only ATEX & IECEX and INMETRO certified.
- Gland size does not necessarily equate to the entry thread size.
- Dimensions (A) & (B) may differ for glands with non metric entry threads. Please refer to our "Thread Reference Tables" for specific dimensions.
- Assembly instructions must be read prior to installation and adhered to in full.
- Peppers supplies cable glands with parallel entry threads that conform to the flameproof threaded joint requirements of IEC/EN 60079-1 and other equivalent standards. They usually incorporate a thread run out according to the available machining techniques and will not have a full form thread for the entire length.

- Peppers Cable Glands Limited will not be held responsible for clients' installations where this has not been taken into account.
- When selecting IP Washer material for gland kits, please be aware of the accessories temperature range to ensure they are suitable for the intended installation.
- Where approval in addition to ATEX, IECEX and CSA is required, this must be clearly requested at time of enquiry / order.